



LEDLENSER MH3/MH4/MH5

MH3








AA

MH4/MH5



14500




5

White mode
(MH3/MH4/MH5)


⌚
hold 3s
⏪|||⏩

Red mode
(MH4/MH5)


Off




Low Power




Power




Off






Off



Red



Off



Ledlenser GmbH & Co. KG
Kronenstr. 5-7 • 42699 Solingen • Germany
Phone +49 212/5948-0 Fax +49 212/5948-200
info@ledlenser.com



MH3/MH4/MH5_V.03
16.08.2019
1J12A0333